

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1511174340](#)  
**Status:** **Active**  
**Overview:** [Milli-Grid Connector System](#)  
**Description:** 2.00mm Pitch, Milli-Grid PCB Header, Dual Row, Vertical, Through Hole, 0.75µm Gold (Au) Plating, without Peg, 3.60mm PC Tail Length, without Pick and Place Cap, 40 Circuits, Glow-Wire Capable, Tube

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 503940002-AS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-151117-0001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification PK-151117-3000 (PDF)</a>
<a href="#">Product Specification PS-151117-0001-001 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Application Specification 503940001-AS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	PCB Headers
Series	<a href="#">151117</a>
Application	Board-to-Board, Signal, Wire-to-Board
Overview	<a href="#">Milli-Grid Connector System</a>
Product Name	Milli-Grid
UPC	889056832915

**Physical**

Breakaway	No
Circuits (Loaded)	40
Circuits (maximum)	40
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	1.821/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.60mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	2.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.750µm
Plating min - Termination	2.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	None
Shrouded	Yes



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
D(2020)4578-DC (25  
June 2020)  
henicosaflooroundecanoic  
acid  
disodium 4-  
amino-3-[[4'-[(2,4-  
diaminophenyl)azo]  
chromium trioxide  
1,3-propanesultone  
1-vinylimidazole  
4,4'-methylenedi-o-  
toluidine  
dibutyltin dichloride  
methoxyacetic acid  
diisopentylphthalate  
disodium 3,3'-[[1,1'-  
biphenyl]-4,4'-  
diylbis(azo)  
octamethylcyclotetrasiloxane  
benzene-1,2,4-  
tricarboxylic acid 1,2-  
anhydride  
decamethylcyclopentasiloxane  
dodecamethylcyclohexasiloxane  
heptacosafloorotetradecanoic  
acid  
tricosafloorododecanoic  
acid  
di-n-pentyl phthalate  
(DPP)  
6-methoxy-m-toluidine  
furan  
1-bromopropane  
nitrobenzene  
4-o-tolylazo-o-  
toluidine  
ethylene thiourea

**China RoHS**

Stackable  
Surface Mount Compatible (SMC)  
Temperature Range - Operating  
Termination Interface: Style

#### Electrical

Current - Maximum per Contact  
Voltage - Maximum

#### Material Info

#### Reference - Drawing Numbers

Application Specification  
Packaging Specification  
Product Specification  
Sales Drawing

No  
Yes  
-55° to +105°C  
Through Hole

2.0A  
125V AC

503940001-AS-000, 503940002-AS-000  
PK-151117-0001-001, PK-151117-3000  
PS-151117-0001-001  
SD-151117-0001-001

4-methyl-m-phenylenediamine  
o-toluidine  
butyl 4-hydroxybenzoate  
dinoseb (ISO)  
dihexyl phthalate (DnHP)  
dicyclohexyl phthalate  
N-methylacetamide  
dimethyl sulphate  
diethyl sulphate  
4-aminoazobenzene  
Fatty acids, C16-18, lead salts  
[phthalato(2-)]dioxotrilead  
Silicic acid (H<sub>2</sub>Si<sub>2</sub>O<sub>5</sub>), barium salt (1:1), lead-  
Perfluorohexane-1-sulphonic acid and its salts  
5-sec-butyl-2-(2,4-dimethylcyclohex-3-en-1-yl)-5  
1,2-benzenedicarboxylic acid, di-C<sub>6</sub>-10-alkyl est  
Cadmium sulphate  
Sodium perborate; perboric acid, sodium salt  
hexahydro-2-benzofuran-1,3-dione  
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated  
Perfluorononan-1-oic acid  
(2,2,3,3,4,4,5,5,6,6,7  
Reaction  
products of 1,3,4-thiadiazolidine-2,5-d  
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o  
Chrysene  
Cadmium nitrate  
Pyrene  
Tris(4-nonylphenyl, branched and linear)  
phosphi  
2,3,3,3-tetrafluoro-2-(heptafluoropropoxy)propio  
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated  
Trixylyl phosphate  
Zirconia  
Aluminosilicate  
Refractory Ceramic  
Fibr  
Aluminosilicate  
Refractory Ceramic  
Fibres  
Boric acid

Disodium tetraborate  
Hydrazine  
1,3-BENZENEDIOL,  
TRINITRO-, LEAD  
SALT  
n-pentyl-  
isopentylphthalate  
3-ethyl-2-methyl-2-  
(3-methylbutyl)-1,3-  
oxazolidi  
1,2-  
benzenedicarboxylic  
acid, dipentylester,  
bra  
pentacosafuorotridecanoic  
acid  
1,2-  
Benzenedicarboxylic  
acid, dihexyl ester,  
bra  
Terphenyl,  
hydrogenated  
2-(2H-benzotriazol-2-  
yl)-4-(tert-butyl)-6-  
(sec-b  
2-(2H-benzotriazol-2-  
yl)-4,6-  
ditertpentylphenol  
dibutylbis(pentane-2,4-  
dionato-O,O')tin  
2-ethylhexyl 10-  
ethyl-4,4-dioctyl-7-  
oxo-8-oxa-3,  
disodium octaborate  
sodium  
peroxometaborate  
ammoniumpentadecafluorooctanoate  
pentazinc chromate  
octahydroxide  
1,2-dichloroethane  
trilead diarsenate  
2-methoxyaniline  
arsenic acid  
N,N-  
dimethylacetamide  
lead dipicrate  
potassium  
hydroxyoctaoxodizincatedichromate(1-)  
bis(2-methoxyethyl)  
ether  
calcium arsenate  
1,2-  
benzenedicarboxylic  
acid; di-C6-8-  
branched a  
N-methyl-2-  
pyrrolidone  
1,2-  
benzenedicarboxylic  
acid; di-C7-11-  
branched  
2-ethoxyethyl acetate  
cobalt sulphate  
cobalt di(acetate)  
cobalt carbonate

tetraboron disodium  
heptaoxide, hydrate  
sodium chromate  
potassium dichromate  
potassium chromate  
ammonium  
dichromate  
tris(2-chloroethyl)  
phosphate  
Lead sulfochromate  
yellow  
Lead chromate  
molybdate sulfate red  
lead chromate  
Anthracene oil,  
anthracene-low;  
Anthracene Oil F  
Anthracene oil,  
anthracene paste,  
distn. lights;  
Anthracene oil,  
anthracene paste,  
anthracene fra  
Anthracene oil,  
anthracene paste;  
Anthracene Oil  
Butylbenzylphthalate  
(BBP)  
lead hydrogen  
arsenate  
bis(2-ethylhexyl)  
phthalate (DEHP)  
dibutyl phthalate  
(DBP)  
4,4'-  
diaminodiphenylmethane  
triethyl arsenate  
Sulfurous acid, lead  
salt, dibasic  
Acetic acid, lead salt,  
basic  
cadmium hydroxide  
Lead titanium  
zirconium oxide  
dioxobis(stearato)trilead  
tetralead trioxide  
sulphate  
trilead dioxide  
phosphonate  
pentalead tetraoxide  
sulphate  
lead oxide sulfate  
Silicic acid, lead salt  
cadmium chloride  
lead dinitrate  
pyrochlore, antimony  
lead yellow  
cadmium fluoride  
cadmium  
lead  
 $\alpha,\alpha'$ Bis[4-  
(dimethylamino)phenyl]-4  
(phenylamino)

[4-[[4-anilino-1-naphthyl][4-(dimethylamino)phenyl,3,5-tris(oxiranylmethyl)-1,3,5-triazine-2,4,6(Lead oxide  
trilead bis(carbonate) dihydroxide  
orange lead  
cadmium sulphide  
cadmium oxide (non-pyrophoric)  
diboron trioxide  
bis(pentabromophenyl) ether  
4,4'-bis(dimethylamino)-4''-(methylamino)trityl  
[4-[4,4'-bis(dimethylamino)benzhydrylidene]cycl  
cadmium carbonate  
1,2-dimethoxyethane  
4,4'-bis(dimethylamino)benzophenone  
dichromium  
tris(chromate)  
phenolphthalein  
lead diazide  
bis(2-methoxyethyl)  
phthalate  
Formaldehyde,  
polymer with  
benzenamine

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[151117 Series](#)

**Mates With**

Milli-Grid Receptacle Housing [151192](#) ,  
[51110](#) <br>Milli-Grid PCB Receptacles  
[78787](#) , [78788](#) , [79107](#) , [79109](#)

This document was generated on 10/13/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**